EPSILON Free walk exerciser



Thanks to its unique design, the Epsilon is an extremely sturdy treadmill. You can relax in the knowledge that your horses are safely exercising on the treadmill.





It requires only a small investment.

- Direct, non-slip drive
- Minimum maintenance needed
- Protected drive unit
- Economical (0.5kW/h)
- Interactive section selection
- Lightweight driving fences with free legroom
- All steel parts are zinc galvanized
- Including walk control box



Options





ERSILON N

EPSILON Free walk exerciser



Technical specifications:

Outside diameter of the Epsilon Number of horses max. Drive

Power supply Energy consumption Conservation

Fasteners

Drift fences performance

Tension Cables Width drift fence Height drift fence Run path / hoof path width Electrical shock device 12 – 20 meter / 39-65.6 ft 3 / 4 / 5 / 6 / 8 horses Direct, non slip drive with safety /

protection coupling

230 Volt AC - 50/60 Hz.; electric mains About 0.5Kw/h

Fully galvanized according to NEN-EN-ISO

1461-99

According DIN / ISO norm, Minimum 8.8,

Electrolytic galvanized

Aluminum lightweight, free movable eventual with Electric shock

Fully galvanized with steel tread inside

2,0 meter / 6.56 ft 2,0 meter / 6.56 ft 2,5 meter / 8.2 ft

Optional

Walk control box

The KYLIX walk control box is designed to provide your horses with safe, thorough, controlled and natural daily exercise on your KYLIX free walk exerciser. The walk control box is easy to control and ready for use

Walk control box

Speed (walk-trot) Section selection Housing of Control box In conformity with Note

Left- and right turn 5 minutes per direction 4-18 km/h interactive

Polyester enclosure IP 65

CE norm

The walk control box comes standard with

the horse exerciser

Programmable walk-trot control box

The KYLIX programmable walk-trot control box is the reliable brain of your KY-LIX free walk exerciser. It enables your horses to train vigorously and safely. The box has a number of preprogrammed sessions, which can easily and quickly be modified to suit your own needs.

Programmable walk-trot control box

Time

Speed

Number of training sessions Number of program steps in one session

Display Section selection Housing of Control box In conformity with Note

Left- and right turn (variable to establish by each program-step)

1 till 20 minutes per program-step variable to establish

(walk - trot) 4-18 km/h 2,5-11,25 mph per program-step variable to establish 6 training sessions, free to program

10 unlimited program steps, including maximum run time safety

Speed, step time and training time interactive

Polyester enclosure IP 65

CE norm

The walk trot control box is optional

The electrical system and gear unit of the KYLIX Epsilon free walk exerciser, will be customized for the electrical system in your region.



P.O. Box 45

NL-7650 AA

Tubbergen

The Netherlands

Newtonstraat 3 B

NL-7651 AP

Tubbergen

The Netherlands

T. +31 546 - 577305

F. +31 546 - 570300

E-mail info@kylix.nl www.kylix.nl



