


EPSILON Free walk exerciser

Thanks to its unique design, the Epsilon is an extremely sturdy treadmill. You can relax in the knowledge that your horses are safely exercising on the treadmill.



It requires only a small investment.

- Direct, non-slip drive
- Minimum maintenance needed
- Protected drive unit
- Economical (0.5kW/h)
- Interactive section selection
- Lightweight driving fences with free legroom
- All steel parts are zinc galvanized
- Including walk control box

INNOVATION - QUALITY - SERVICE



Options



EPSILON

EPSILON

EPSILON Free walk exerciser

Technical specifications:

Outside diameter of the Epsilon	12 – 20 meter / 39-65.6 ft
Number of horses max.	3 / 4 / 5 / 6 / 8 horses
Drive	Direct, non slip drive with safety / protection coupling
Power supply	230 Volt AC – 50/60 Hz.; electric mains
Energy consumption	About 0.5Kw/h
Conservation	Fully galvanized according to NEN-EN-ISO 1461-99
Fasteners	According DIN / ISO norm, Minimum 8.8, Electrolytic galvanized
Drift fences performance	Aluminum lightweight, free movable eventual with Electric shock
Tension Cables	Fully galvanized with steel tread inside
Width drift fence	2,0 meter / 6.56 ft
Height drift fence	2,0 meter / 6.56 ft
Run path / hoof path width	2,5 meter / 8.2 ft
Electrical shock device	Optional

Walk control box

The KYLIX walk control box is designed to provide your horses with safe, thorough, controlled and natural daily exercise on your KYLIX free walk exerciser. The walk control box is easy to control and ready for use

Walk control box

Time	Left- and right turn can be changed by yourself between 1 minutes and 3 hours
Speed (walk-trot)	4-16 km/h
Housing of Control box	Polyester enclosure IP 65
In conformity with	CE norm
Note	The walk control box comes standard with the horse exerciser

Programmable walk-trot control box

The KYLIX programmable walk-trot control box is the reliable brain of your KYLIX free walk exerciser. It enables your horses to train vigorously and safely. The box has a number of preprogrammed sessions, which can easily and quickly be modified to suit your own needs.

Programmable walk-trot control box

Time	Left- and right turn (variable to establish by each program-step) Can be changed by yourself between 1 minutes and 3 hours
Speed (walk – trot)	4-16 km/h per program-step variable to establish 6 training sessions, free to program
Number of training sessions	10 unlimited program steps, including maximum run time safety
Number of program steps in one session	Speed, step time and training time interactive
Display	Polyester enclosure IP 65
Section selection	CE norm
Housing of Control box	The walk trot control box is optional
In conformity with	
Note	

The electrical system and gear unit of the KYLIX Epsilon free walk exerciser, will be customized for the electrical system in your region.

